



TXA210N

### Dimmer 1 channel 600W

#### Technical Features

##### Voltage

System supply voltage	30 V DC Via bus
-----------------------	-----------------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

##### Connection

Cross-section flexible conductor	0.75 - 2.5 mm <sup>2</sup>
----------------------------------	----------------------------

Cross-section rigid conductor	0.75 - 2.5 mm <sup>2</sup>
-------------------------------	----------------------------

##### Equipment

Number of outputs	1
-------------------	---

Type of dimmer	Universal
----------------	-----------

##### Capacity

Number of modules	4
-------------------	---

##### Power

Power incandescent lamp	20 - 600 W
-------------------------	------------

Power of variator	0 - 600 W
-------------------	-----------

##### Connectivity

Type of connection	quickconnect
--------------------	--------------

##### Settings

Supported configuration mode	ETS easy
------------------------------	-------------