



FWB71GS

FWB encl. univers,surface mount.,IP44,classII,w. transp.door;1100x300x161mm,QC

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	7
Number of rows	7
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	84
-------------------	----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	1100 mm
Width	300 mm
Depth	165 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	1

#### Dimensions

Number of width units	12
-----------------------	----

#### Cover, door

Type of handle	Latch
Door/cover is transparent	Yes

#### Connection

Number of conduit inlets	4
--------------------------	---

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP44

#### Sustainability

RoHS conform	Yes
--------------	-----