



IP55 13A SWITCHED SOCKET

Technical Features

Voltage

Rated voltage 250 V

Electric current

Rated current 13 A

Dimensions

Height 91.50 mm

Width 110 mm

Depth 67.50 mm

Installation, mounting

Mounting on Surface mounting

Equipment

Rotated central insert No

With hinged lid No

Safety

Ingress Protection (IP) class IP55