



DBS2453300ELN

**Installation column pressure fit, double sided, height 3.3-3.6m,Clip45, anodized**

**Technical Features**

**Dimensions**

Depth	130 mm
Width	65 mm
Installation height	3.3 - 3.6 m
Height adjustment	300 mm
Inner cross-section	5300 - 5300 mm <sup>2</sup>
Pole shape	Rectangular
Lid width	45 mm

**Cover, door**

Number of mountable lids	2
--------------------------	---

**Equipment**

Adjustable	Yes
Is portable	No

**Cable**

Cable entry position	Top
----------------------	-----

**Installation, mounting**

Ceiling mounting possible	Yes
Suitable for ground mounting	Yes

**Materials**

Material	Aluminium
Treatment	Anodised
Colour	Aluminium

**Configuration**

Number of sides for installation	Double side
----------------------------------	-------------

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

