



DBS2453300ELN

Installation column pressure fit, double sided, height 3.3-3.6m,Clip45, anodized

Technical Features

Dimensions

Depth	130 mm
Width	65 mm
Installation height	3.3 - 3.6 m
Height adjustment	300 mm
Inner cross-section	5300 - 5300 mm ²
Pole shape	Rectangular
Lid width	45 mm

Cover, door

Number of mountable lids	2
--------------------------	---

Equipment

Adjustable	Yes
Is portable	No

Cable

Cable entry position	Top
----------------------	-----

Installation, mounting

Ceiling mounting possible	Yes
Suitable for ground mounting	Yes

Materials

Material	Aluminium
Treatment	Anodised
Colour	Aluminium

Configuration

Number of sides for installation	Double side
----------------------------------	-------------

Sustainability

RoHS conform	Yes
--------------	-----

Illustrations | Drawings

