



VMLF14

Design 10, Flush 14 Way HI 100A Sw 2*100A 30mA RCCB Type A SPD

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Architecture

Number of poles	2
-----------------	---

Functions

Has protection main switch	Yes
Overvoltage protection	Yes

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Capacity

Number of modules	14
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	104 mm
Height	282 mm
Width	515 mm
Thickness of sidewall	1 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	2
-----------------------------	---

Equipment

Number of rows	1
Number of rails	1
Extension possible	No
With socket outlet	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC
Number of earth leakage switches 300 mA	0