



SR600

**Current transformer 600 / 5A**

**Technical Features**

**Functions**

Accuracy class	1
----------------	---

**Power**

Power	15 VA
Total power loss under I <sub>N</sub>	0 W

**Dimensions**

Diameter of opening	10 mm
Height	70 mm
Width	77 mm
Depth	75 mm
Height of opening	40 mm
Width of opening	35 mm

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Use conditions**

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 80 °C

**Connection**

Cross-section flexible conductor	1.5 - 4 mm <sup>2</sup>
Cross-section rigid conductor	2.5 - 6 mm <sup>2</sup>

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Electric current**

Max. intensity of primary	720 A
Max. intensity of secondary	5 A

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes