



SR600

Current transformer 600 / 5A

Technical Features

Functions

Accuracy class	1
----------------	---

Power

Power	15 VA
Total power loss under I _N	0 W

Dimensions

Diameter of opening	10 mm
Height	70 mm
Width	77 mm
Depth	75 mm
Height of opening	40 mm
Width of opening	35 mm

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Use conditions

Operating temperature	-25 - 50 °C
Storage/transport temperature	-40 - 80 °C

Connection

Cross-section flexible conductor	1.5 - 4 mm ²
Cross-section rigid conductor	2.5 - 6 mm ²

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Electric current

Max. intensity of primary	720 A
Max. intensity of secondary	5 A

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes