



47452089

**SCHUKO soc. out., mounting orient. var. in 45° steps, R.classic, p. white glossy**

#### Technical Features

##### Electric current

Rated current	16 A
---------------	------

##### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

##### Dimensions

Height	71 mm
Width	71 mm
Depth	42 mm
Number of units	1
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

##### Connection

Connector/plug type	Plug clamp
---------------------	------------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

##### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

##### Functions

With orientation lighting	No
With function lighting	No

<b>Texts</b>	
Imprint	Without imprint
Cover	Central cover plate
Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

<b>Suitable for</b>	
R.x / Serie R.classic	

<b>Sustainability</b>	
Halogen free	Yes
RoHS conform	Yes