



WXF001

Intermediate switch gallery 2 modules

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Middle plate
----------------------	--------------

Connectivity

Mounting type	Click mounting Screwless
---------------	-----------------------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	45 x 45 mm
Built-in depth	40 mm
Built-in depth flush-mounted boxes	40 mm

Safety

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

Electric current

Rated current	10 A
---------------	------

Connection

Type of contacts	2-way
------------------	-------

Texts

Lighting	For illumination with LED module
Switch mode	Intermediate switch

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes