



WXF001

**Intermediate switch gallery 2 modules**

**Technical Features**

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Grey
RAL code	7011
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

**Identification**

Assembly arrangement	Middle plate
----------------------	--------------

**Connectivity**

Mounting type	Click mounting Screwless
---------------	-----------------------------

**Controls and indicators**

Number of buttons	1
-------------------	---

**Dimensions**

Dimensions	45 x 45 mm
Built-in depth	40 mm
Built-in depth flush-mounted boxes	40 mm

**Safety**

Ingress Protection (IP) class	IP21
Impact resistance IK	IK05

**Electric current**

Rated current	10 A
---------------	------

**Connection**

Type of contacts	2-way
------------------	-------

**Texts**

Lighting	For illumination with LED module
Switch mode	Intermediate switch

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes