



20446089



Thermostat, NO contact, centre plate, time-controlled, Q.1, p. white velvety

Technical Features

Installation, mounting

Mounting on Flush mounting

Settings

Comfort temperature setpoint 10 - 40 °C

Dimensions

Height 71 mm
Width 71 mm
Depth 42 mm

Power supply

Supply voltage 230 V AC

Voltage

Nominal voltage 230 - 230 V

Electric current

Max. switching current 10 A

Materials

Colour Polar white

Power

Standby power consumption (solstandby) 1.20 W

Use conditions

Energy efficiency class IV (2%)

Sustainability

Halogen free Yes
REACH-SVHC free Yes
RoHS conform Yes