



20446084



Thermostat, NO cont., w. centre plate, time-controlled, Q.x, alu velvety, lacq.

Technical Features

Installation, mounting

Mounting on Flush mounting

Settings

Comfort temperature setpoint 10 - 40 °C

Dimensions

Height 71 mm  
Width 71 mm  
Depth 42 mm

Voltage

Nominal voltage 230 - 230 V

Materials

Colour Aluminium

Use conditions

Energy efficiency class IV (2%)

Sustainability

REACH-SVHC free Yes  
RoHS conform Yes