



FW512WT

Surface encl. FW2, IP30, class I, with door and brass terminals, 5x12 modules

### Technical Features

#### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

#### Equipment

|                            |    |
|----------------------------|----|
| Number of rows             | 5  |
| Number of section in width | 1  |
| With lock                  | No |
| Has neutral terminal block | No |

#### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 72 |
|-------------------|----|

#### Dimensions

|        |        |
|--------|--------|
| Height | 941 mm |
| Width  | 355 mm |
| Depth  | 150 mm |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 12 |
|-----------------------|----|

#### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

#### Connection

|                          |   |
|--------------------------|---|
| Number of conduit inlets | 1 |
|--------------------------|---|

#### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

#### Safety

|                               |                          |
|-------------------------------|--------------------------|
| Protection class              | Isolation class I        |
| Impact resistance IK          | IK08                     |
| Ingress Protection (IP) class | IP30                     |
| Locking type                  | Key lock<br>Without lock |