



260209



**230 V USB charging socket outlet, 2gang, 3.0A, angular supporting ring, pw.**

**Technical Features**

**Connectivity**

Type of connection	Screw terminal
Connector/plug type USB	A

**Dimensions**

Built-in depth	32 mm
Built-in depth flush-mounted boxes	34 mm

**Equipment**

Number of outputs	2
-------------------	---

**Accessories**

Has labelling field	No
With miniature fuse	No

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Matt

**Power**

Output power	15 W
Power consumption standby	0.15 W

**Voltage**

Input voltage	230 - 230 V
Output voltage	5 - 5 V

**Electric current**

Rated current	0.20 A
Output current	3000 mA

**Texts**

Connectors jacks	With 2 USB sockets type A
Fuse	Short-circuit and overload-proof (electronic fuse)
Type of connection	With screw terminals
Protection	Without enhanced contact protection

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes