



47501606

## SCHUKO soc. out., B.3/B.7, ant., matt

### Technical Features

#### Electric current

Rated current	16 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Materials

Colour	Anthracite
RAL code	7021
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

#### Dimensions

Height	71 mm
Width	71 mm
Number of units	1
Built-in depth	32 mm

#### Connection

Connector/plug type	Plug clamp
---------------------	------------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting Claw mounting

#### Equipment

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

#### Accessories

Has labelling field	Yes
---------------------	-----

#### Capacity

Number of modules	1
-------------------	---

#### Safety

With enhanced contact protection	No
Impact resistance IK	IK05
Ingress Protection (IP) class	IP20

#### Functions

With orientation lighting	No
With function lighting	No

#### Texts

Imprint	Without imprint
Cover	Central cover plate

**Texts**

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Labelling	With labelling field

**Suitable for**

S.x/B.x
---------

**Sustainability**

Halogen free	Yes
RoHS conform	Yes