



47501606

**SCHUKO soc. out., B.3/B.7, ant., matt**

**Technical Features**

**Electric current**

Rated current	16 A
---------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

Nominal voltage	250 - 250 V
-----------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Anthracite
--------	------------

RAL code	7021
----------	------

Surface finish	Matt
----------------	------

Material	Thermoplastic
----------	---------------

Treatment	Untreated
-----------	-----------

**Dimensions**

Height	71 mm
--------	-------

Width	71 mm
-------	-------

Number of units	1
-----------------	---

Built-in depth	32 mm
----------------	-------

**Connection**

Connector/plug type	Plug-in terminal
---------------------	------------------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Plug-in connection
--------------------	--------------------

Mounting type	Screw mounting Claw mounting
---------------	---------------------------------

**Equipment**

Connector/plug type socket outlet	SCHUKO
-----------------------------------	--------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

With signal lamp	No
------------------	----

With lock	No
-----------	----

**Accessories**

Has labelling field	Yes
---------------------	-----

**Capacity**

Number of modules	1
-------------------	---

**Safety**

With enhanced contact protection	No
----------------------------------	----

Impact resistance IK	IK05
----------------------	------

Ingress Protection (IP) class	IP20
-------------------------------	------

**Functions**

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

**Texts**

Imprint	Without imprint
---------	-----------------

Cover	Central cover plate
-------	---------------------

**Texts**

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals
Labelling	With labelling field

**Suitable for**

S.x/B.x

**Sustainability**

Halogen free	Yes
RoHS conform	Yes