



JVC4800S25TW

250A TPN board, INVICTA, 48P Chassis , ISO-STD-GR

Technical Features

Connection

Number of accessible phases	48
-----------------------------	----

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	250 A
Breaking and opening capacity Idm	0 kA

Equipment

With lock	Yes
Has mounting plate	No
Equipped with switch	Isolator
Number of switches	1
Type of busbar chassis	Fixed load chassis

Capacity

Number of modules	16
-------------------	----

Dimensions

Height	1000 mm
Width	480 mm
Depth	135 mm

Cover, door

Door/cover is transparent	No
---------------------------	----

Materials

Material	Steel
RAL code	7035
Colour	Light grey

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock With lock

Architecture

Number of poles	48
-----------------	----

Sustainability

REACH-SVHC free	Yes
-----------------	-----