



JK216BDFG

JK216 96 Module Side DIN Box Glazed

Technical Features

Installation, mounting

| | |
|----------------------------|------------------|
| Suitable for outdoor usage | No |
| Mounting on | Surface mounting |

Electric current

| | |
|---------------|-------|
| Rated current | 250 A |
|---------------|-------|

Equipment

| | |
|----------------------------|-----|
| Number of rows | 6 |
| With lock | Yes |
| Has neutral terminal block | Yes |

Capacity

| | |
|-------------------|----|
| Number of modules | 96 |
|-------------------|----|

Dimensions

| | |
|--------|-----------|
| Height | 1250 mm |
| Width | 465 mm |
| Depth | 165.50 mm |

Cover, door

| | |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

Dimensions

| | |
|-----------------------|----|
| Number of width units | 96 |
|-----------------------|----|

Cover, door

| | |
|---------------------------|-----|
| Door/cover is transparent | Yes |
|---------------------------|-----|

Materials

| | |
|----------|------------|
| Material | Steel |
| RAL code | 7035 |
| Colour | Light grey |

Equipment

| | |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

Safety

| | |
|-------------------------------|-------------------------------|
| Protection class | Isolation class III |
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP3X |
| Locking type | Key lock Quarter turn lock |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|