



JK216BDFG

**JK216 96 Module Side DIN Box Glazed**

**Technical Features**

**Installation, mounting**

Suitable for outdoor usage	No
Mounting on	Surface mounting

**Electric current**

Rated current	250 A
---------------	-------

**Equipment**

Number of rows	6
With lock	Yes
Has neutral terminal block	Yes

**Capacity**

Number of modules	96
-------------------	----

**Dimensions**

Height	1250 mm
Width	465 mm
Depth	165.50 mm

**Cover, door**

Number of cabinet doors	1
-------------------------	---

**Dimensions**

Number of width units	96
-----------------------	----

**Cover, door**

Door/cover is transparent	Yes
---------------------------	-----

**Materials**

Material	Steel
RAL code	7035
Colour	Light grey

**Equipment**

Has earthing terminal block	Yes
-----------------------------	-----

**Safety**

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP3X
Locking type	Key lock Quarter turn lock

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes