



EU102

control relay monophased voltage 230V

Technical Features

Capacity

Number of modules	2
-------------------	---

Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-40 - 70 °C

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Dimensions

Height	85 mm
Width	35 mm
Depth	60 mm

Power supply

Supply voltage	3N, 400/230 V
----------------	---------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Safety

Ingress Protection (IP) class	IP30
-------------------------------	------

Power

Power	5 VA
Total power loss under IN	4 W

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Electric current

Acceptable current rating AC1	8 A
-------------------------------	-----

Installation, mounting

Mounting on	DIN rail
-------------	----------

Settings

Switch off delay time	1200 s
-----------------------	--------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes