




WGML121PAS

10A 2G press switch;as

Technical Features

Electric current	
Switching current	10 A

Voltage	
Rated voltage	250 V

Architecture	
Control/operation element	Double rocker

Materials	
Colour	Aurora silver
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished
Transparent	No

Dimensions	
Height	86 mm
Width	86 mm
Depth	25 mm
Built-in depth flush-mounted boxes	35 mm

Controls and indicators	
Number of buttons	2

Connectivity	
Type of connection	Screw terminal

Safety	
Ingress Protection (IP) class	IP20

Accessories	
Has labelling field	No

Suitable for	
shark	

Sustainability	
RoHS conform	Yes