



JF608B

**800A 8 Way 4\*250A + 4\*125A Plain**

**Technical Features**

**Installation, mounting**

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

**Electric current**

|               |       |
|---------------|-------|
| Rated current | 800 A |
|---------------|-------|

**Equipment**

|                            |     |
|----------------------------|-----|
| With lock                  | Yes |
| Has neutral terminal block | Yes |

**Dimensions**

|        |         |
|--------|---------|
| Height | 1250 mm |
| Width  | 900 mm  |
| Depth  | 220 mm  |

**Cover, door**

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

**Materials**

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 7035       |
| Colour   | Light grey |

**Equipment**

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
|-----------------------------|-----|

**Safety**

|                               |                         |
|-------------------------------|-------------------------|
| Protection class              | Isolation class III     |
| Impact resistance IK          | IK05                    |
| Ingress Protection (IP) class | IP30                    |
| Locking type                  | Barrel lock<br>Key lock |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|