



FR11E2

**Steel enclosure, Unipers, IP55, CL1, 1700x300x275 mm, plinth H200 mm**

**Technical Features**

**Dimensions**

Height	1900 mm
Width	300 mm
Depth	275 mm
Thickness of sidewall	1.50 mm

**Safety**

Ingress Protection (IP) class	IP55
Protection class	Isolation class I
Locking type	Without lock
Impact resistance IK	IK10

**Equipment**

Number of section in width	1
Number of flange plate openings	2

**Installation, mounting**

Mounting on	Floor mounting
Suitable for outdoor usage	No

**Materials**

Colour	Light grey
RAL code	7035
Treatment	Powder coated
Material	Steel

**Equipment**

Number of rows	11
----------------	----

**Materials**

Surface finish	Matt
----------------	------

**Cover, door**

Number of cabinet doors	1
Number of locks	1
Door/cover is transparent	No

**Electric current**

Rated current	800 A
---------------	-------

**Voltage**

Nominal voltage	690 - 690 V
-----------------	-------------

**Sustainability**

RoHS conform	Yes
--------------	-----