



16617109

Rocker f. accessible const., guide f. mouth-held rod, lens, K.1, p.white glossy

Technical Features

Architecture

Control/operation element	Rocker with mouth rod guiding
---------------------------	-------------------------------

Materials

Colour	Polar white
RAL code	9010
Surface finish	Glossy
Material	Thermoplastic
Treatment	Untreated

Dimensions

Height	54.90 mm
Width	55.70 mm
Depth	22 mm

Connectivity

Mounting type	Clamp mounting
---------------	----------------

Equipment

Monitoring window/light outlet	Yes
--------------------------------	-----

Accessories

Has labelling field	No
---------------------	----

Safety

Ingress Protection (IP) class	IP44
Impact resistance IK	IK05

Texts

Imprint	Without imprint
Installation mode	Clamp fastening
Lighting	For lighting and monitoring circuit
Push button	Also for KNX applications: push-button, 1-gang, and group push-button, 1-gang
Rocker switch/rocker push-button	For rocker push-buttons For change-over/intermediate switch

Suitable for

K.x

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes