



WGMT1RJ6NM

RJ45 outlet cat6 (1mod) wo/symbol

Technical Features

Frequency

| | |
|------------------------|-----------|
| Transmission bandwidth | 0-250 MHz |
|------------------------|-----------|

Equipment

| | |
|-------------------------------|----|
| With transparent label holder | No |
| Number of outputs | 1 |

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | -20-45 °C |
|-----------------------|-----------|

Equipment

| | |
|-----------------|----|
| With hinged lid | No |
|-----------------|----|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Connection

| | |
|---------------------|------|
| Connector/plug type | RJ45 |
|---------------------|------|

Materials

| | |
|----------|--------------------|
| Material | Polycarbonate (PC) |
|----------|--------------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Voltage

| | |
|---------------|-----|
| Rated voltage | 0 V |
|---------------|-----|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|