



dr96s4

### Din rail board, 6 row 96M, non-transparent door, surface

#### Technical Features

##### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 415 - 415 V |
|-----------------|-------------|

##### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

##### Power

|                                                  |         |
|--------------------------------------------------|---------|
| Maximum power loss per cabinet at $\Delta T=20K$ | 48.78 W |
|--------------------------------------------------|---------|

##### Equipment

|                            |     |
|----------------------------|-----|
| Number of rails            | 6   |
| Number of rows             | 6   |
| With lock                  | No  |
| Has neutral terminal block | Yes |

##### Capacity

|                                           |    |
|-------------------------------------------|----|
| Number of modules                         | 96 |
| Number of half modules terminals per rail | 32 |

##### Functions

|                            |     |
|----------------------------|-----|
| Has protection main switch | No  |
| With conduit inlets        | Yes |

##### Dimensions

|                 |         |
|-----------------|---------|
| Height          | 1074 mm |
| Width           | 405 mm  |
| Depth           | 115 mm  |
| Built-in height | 1070 mm |
| Built-in width  | 400 mm  |

##### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
|-------------------------|---|

##### Dimensions

|                |        |
|----------------|--------|
| Built-in depth | 110 mm |
|----------------|--------|

##### Cover, door

|                 |   |
|-----------------|---|
| Number of locks | 0 |
|-----------------|---|

##### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 16 |
|-----------------------|----|

##### Cover, door

|                           |    |
|---------------------------|----|
| Door/cover is transparent | No |
|---------------------------|----|

##### Connection

|                          |    |
|--------------------------|----|
| Number of conduit inlets | 17 |
|--------------------------|----|

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9010       |
| Colour   | Grey white |

##### Equipment

|                             |    |
|-----------------------------|----|
| Has earthing terminal block | No |
| Has mounting plate          | No |

**Safety**

|                               |                   |
|-------------------------------|-------------------|
| Protection class              | Isolation class I |
| Impact resistance IK          | IK05              |
| Ingress Protection (IP) class | IP40              |
| Locking type                  | Without lock      |
| Glow wire test                | 960 °C            |

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|