



LFF4009009016

Trunking LFF 40x90mm with coupling and 2 cable clips traffic white

Technical Features

Dimensions

Height	40 mm
Width	90 mm
Length	2000 mm
Inner cross-section	2650 - 2650 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	14
--	----

Materials

Material	Polyvinylchloride (PVC)
Treatment	Untreated
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 60 °C
-----------------------	------------

Connectivity

Trunking coupling	Pre-equipped with couplers
-------------------	----------------------------

Equipment

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	1
Cable retaining clip included	Yes
With protective film	Yes

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes