



BF226N

Earth leakage add-on block 2P 25A 300mA AC Class

Technical Features

Architecture

Neutral position	Right
Number of poles	2

Capacity

Number of modules	2
-------------------	---

Voltage

Rated operational voltage U_e	230 - 400 V
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Electric current

Rated residual operating current I_{dn}	300 mA
Rated current	25 A

Connectivity

Down connection alignment for modular devices	Aligned terminal
---	------------------

Installation, mounting

Nominal tightening torque	2.20 - 2.20 Nm
Nominal tightening torque down terminal	2.20 - 2.20 Nm

Dimensions

Height	70 mm
Width	35 mm
Depth	92 mm