



VML\_SIZE\_7

**Design 10 Consumer Unit 18 Way 100A Sw Disconnecter Incomer Round KO + T2 SPD**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Architecture**

Number of poles	2
-----------------	---

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Installation, mounting**

Suitable for outdoor usage	No
----------------------------	----

**Capacity**

Number of modules	18
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	100 mm
Height	98.20 mm
Width	476 mm
Thickness of sidewall	1 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	9010
Colour	Pure white
Material	Steel

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

Number of rows	1
Number of rails	1
Extension possible	No
With socket outlet	No

**Safety**

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC
Number of earth leakage switches 300 mA	0

**Sustainability**

RoHS conform	Yes
--------------	-----