



HNB160U

Moulded Case Circuit Breaker X250 3P 40kA 160A TM

Technical Features

Electric current

Rated current	160 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 690 V AC IEC 60947-2	4 kA
Rated current 10°C according to IEC 60947	189.40 A
Rated current 15°C according to IEC 60947	185.90 A
Rated current 20°C according to IEC 60947	182.40 A
Rated current 25°C according to IEC 60947	178.70 A
Rated current 30°C according to IEC 60947	175.20 A
Rated current at 35°C according to IEC 60947	171.50 A
Rated current at 40°C according to IEC 60947	167.80 A
Rated current 45°C according to IEC 60947	163.80 A
Rated current 50°C according to IEC 60947	160 A
Rated current 55°C according to IEC 60947	156 A
Rated current at 60°C according to IEC 60947	152 A
Rated current 65°C according to IEC 60947	147.60 A
Rated current 70°C according to IEC 60947	143.50 A

Architecture

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in

Tripping

Response time when opening	10 ms
----------------------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Voltage

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	800 V
Rated operational voltage Ue	220 - 415 V

Functions

Trip unit	TM A/A
-----------	--------

Power

Total power loss under IN	32.60 W
---------------------------	---------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Safety

Ingress Protection (IP) class	IP4X
-------------------------------	------

Connection

Cross-section flexible conductor	35 - 150 mm ²
Cross-section rigid conductor	35 - 185 mm ²

Settings

Thermal protection knob setting xIN	0.63 0.8 1
Adjustment range short-term delayed short-circuit release	0 - 0 A

Compatibility

Suitable for DIN Rail	No
-----------------------	----

Installation, mounting	
Mounting-/Connection Position	Front
Nominal tightening torque	12 - 12 Nm
Main electrical attributes	
Magnetic protection trip time	0 - 0 ms
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes