



384103



Rotary switch/blinds 1pole

Technical Features

Controls and indicators

| | |
|----------------------------|---------------|
| Venetian blind switch type | 1-pole switch |
|----------------------------|---------------|

Materials

| | |
|----------|------------------|
| Material | Metal Plastic |
|----------|------------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Electric current

| | |
|-------------------|------------------------|
| Switching current | 10 AX (100W LED (SBL)) |
| Switching current | 10 A |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|--------------------|-------------------------|
| Switch mode | With neutral position |
| Type of connection | With screw terminals |
| Installation mode | With spreader claws |
| Function | With push lock function |

Suitable for

| |
|-----------------------------------------------------------------|
| B.3 / B.7 / K.1 / K.5 / Q.1 / Q.3 / Q.7 / R.1 / R.3 / R.8 / S.1 |
|-----------------------------------------------------------------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|