



941852501

**SCHUKO socket outlet, with screw terminals, Integro module inserts, brown matt**

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Colour Brown

RAL code 8017

Surface finish Matt

Material Thermoplastic

Treatment Untreated

**Dimensions**

Height 55.50 mm

Width 55.50 mm

Number of units 1

Built-in depth flush-mounted boxes 32 mm

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Screw terminal

Mounting type Built in installation  
Screw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection No

Impact resistance IK IK05

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Identification**

With imprint No

**Texts**

Cover Central cover plate

Protection Without enhanced contact protection

Type of connection With screw terminals

---

**Suitable for**

integro

---

**Sustainability**

---

Halogen free

Yes

---

RoHS conform

Yes

---