



REN610X



### VIDEO module built-in 2-wire stainless steel matt modesta

#### Technical Features

##### Connectivity

Mounting type	Built in installation
---------------	-----------------------

##### Materials

Surface finish	Matt
Material	Metal Stainless steel

##### Controls and indicators

Number of call buttons	0
------------------------	---

##### Voltage

Operating voltage	24 - 24 V
-------------------	-----------

##### Power

Power consumption during operation	5.80 VA
------------------------------------	---------

##### Dimensions

Dimensions	120 x 120 mm
Height	120 mm
Width	120 mm
Depth	36 mm
Camera dome diameter	33 mm

##### Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C

##### Power

Power consumption standby	0.14 W
---------------------------	--------

##### Functions

Function	Viewing
----------	---------

##### Compatibility

Installation technique for door communication	2-wire
---	--------

##### Connection

Conductor cross-section	0 - 0 mm <sup>2</sup>
-------------------------	-----------------------

##### Equipment

Modular construction	Yes
----------------------	-----

##### Texts

Installation mode	Installation in surface-mounted or flush-mounted housings
Junction	Pluggable connection terminal block with screw terminals Connection for module Connecting cable
Lighting	Invisible, glare-free IR LED night lighting
Protection	Loudspeaker and microphone protected against sabotage