



REN610X



VIDEO module built-in 2-wire stainless steel matt modesta

Technical Features

Connectivity

Mounting type	Built in installation
---------------	-----------------------

Materials

Surface finish	Matt
Material	Metal Stainless steel

Controls and indicators

Number of call buttons	0
------------------------	---

Voltage

Operating voltage	24 - 24 V
-------------------	-----------

Power

Power consumption during operation	5.80 VA
------------------------------------	---------

Dimensions

Dimensions	120 x 120 mm
Height	120 mm
Width	120 mm
Depth	36 mm
Camera dome diameter	33 mm

Use conditions

Operating temperature	-20 - 55 °C
Storage/transport temperature	-30 - 80 °C

Power

Power consumption standby	0.14 W
---------------------------	--------

Functions

Function	Viewing
----------	---------

Compatibility

Installation technique for door communication	2-wire
---	--------

Connection

Conductor cross-section	0 - 0 mm ²
-------------------------	-----------------------

Equipment

Modular construction	Yes
----------------------	-----

Texts

Installation mode	Installation in surface-mounted or flush-mounted housings
Junction	Pluggable connection terminal block with screw terminals Connection for module Connecting cable
Lighting	Invisible, glare-free IR LED night lighting
Protection	Loudspeaker and microphone protected against sabotage