



EW025\_J

**Industrial contactor 26A-AC3 / coil 230V AC 50 Hz**

**Technical Features**

**Architecture**

Type of pole	3P
--------------	----

**Voltage**

Rated operational voltage Ue	660 - 660 V
Command voltage AC	230 - 230 V
Command voltage DC	0 - 0 V
Rated insulation voltage Ui	660 V

**Electric current**

Rated operational current Ie under 3P 220 - 230 V AC3 according to IEC 60947 - 4	27 A
Acceptable current rating AC3	26 A
Rated operational current Ie under 3P 380 - 400 V AC AC3 according to IEC 60947 - 4	26 A

**Dimensions**

Depth	92 mm
-------	-------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Rated operational power for 3P under 220 - 230 V AC AC3 according to IEC 60947 - 4	39 kW
--	-------

**Endurance**

Number of mechanical operations	5000000
Electric endurance in number of cycles	500000

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Equipment**

Number of auxiliary contacts as normally open contact	1
Number of auxiliary contacts as normally closed contact	1
Number of NO contacts	3
Number of NC contacts	0

**Use conditions**

Operating temperature	-20 - 55 °C
Storage/transport temperature	-40 - 80 °C

**Connection**

Cross-section of input and output with screws, for flexible conductors	2.5 - 10.0 mm <sup>2</sup>
Cross-section of input and output with screws, for massive conductors	2.5 - 10.0 mm <sup>2</sup>

**Sustainability**

Halogen free	Yes
RoHS conform	Yes