



286010

Rotary dimmer house electronics

Technical Features

Voltage	
Operating voltage	230 - 230 V
Frequency	
Frequency	50 - 60 Hz
Materials	
Material	Metal Plastic
Dimensions	
Diameter axis	4 mm
Height	71 mm
Width	71 mm
Architecture	
Control/operation element	Push & rotative switch
Texts	
Dimming principle	Phase cut-on
Fuse	Short-circuit and overload-proof (fine-wire fuse)
Installation mode	With spreader claws
Type of connection	With screw terminals
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes