



GD118A

Enclosure,gamma,surface mounting,18 Modules, version France

### Technical Features

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	18
-------------------	----

#### Dimensions

Height	250 mm
Width	355 mm
Depth	103 mm

#### Cover, door

Number of cabinet doors	0
Number of locks	0

#### Dimensions

Number of width units	18
-----------------------	----

#### Cover, door

Door/cover is transparent	No
---------------------------	----

#### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	Yes

#### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	850 °C

#### Sustainability

RoHS conform	Yes
--------------	-----