



EPN053

**Auxiliary for control by maintained contact**

**Technical Features**

**Electric current**

Rated current	2 A
---------------	-----

**Capacity**

Number of modules	0.50
-------------------	------

**Use conditions**

Operating temperature	-5 - 40 °C
-----------------------	------------

Storage/transport temperature	-40 - 80 °C
-------------------------------	-------------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
----------------------------------	-----------------------

Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
-------------------------------	--------------------------

**Power**

Total power loss under IN	0.10 W
---------------------------	--------

**Dimensions**

Height	85 mm
--------	-------

Width	8.90 mm
-------	---------

Depth	64 mm
-------	-------

**Sustainability**

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----