



EPN051

Auxiliary contact 1NC+1NO

Technical Features

Electric current	
Rated current	2 A
Voltage	
Rated insulation voltage Ui	250 V
Capacity	
Number of modules	0.50
Use conditions	
Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C
Connectivity	
Type of connection	Screw terminal
Connection	
Cross-section flexible conductor	1 - 6 mm²
Cross-section rigid conductor	1.5 - 10 mm²
Type of contacts	1NC+1NO
Power	
Total power loss under IN	0.10 W
Dimensions	
Height	83 mm
Width	8.75 mm
Depth	58 mm
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

