



EPN050

**Auxiliary contact for centralised control**

**Technical Features**

**Electric current**

Rated current	1 A
---------------	-----

**Capacity**

Number of modules	0.50
-------------------	------

**Use conditions**

Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Connection**

Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>

**Power**

Total power loss under IN	0.10 W
---------------------------	--------

**Dimensions**

Height	85 mm
Width	8.90 mm
Depth	58 mm

**Sustainability**

RoHS conform	Yes
--------------	-----

**Illustrations | Drawings**

