



EPN050

Auxiliary contact for centralised control

Technical Features

Electric current	
Rated current	1 A
Capacity	
Number of modules	0.50
Use conditions	
Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C
Connectivity	
Type of connection	Screw terminal
Connection	
Cross-section flexible conductor	1 - 6 mm²
Cross-section rigid conductor	1.5 - 10 mm²
Power	
Total power loss under IN	0.10 W
Dimensions	
Height	85 mm
Width	8.90 mm
Depth	58 mm
Sustainability	
RoHS conform	Yes

Illustrations | Drawings

