



EPN050

**Auxiliary contact for centralised control**

**Technical Features**

**Electric current**

Rated current 1 A

**Capacity**

Number of modules 0.50

**Use conditions**

Operating temperature -5 - 40 °C

Storage/transport temperature -40 - 80 °C

**Connectivity**

Type of connection Screw terminal

**Connection**

Cross-section flexible conductor 1 - 6 mm<sup>2</sup>

Cross-section rigid conductor 1.5 - 10 mm<sup>2</sup>

**Power**

Total power loss under IN 0.10 W

**Dimensions**

Height 85 mm

Width 8.90 mm

Depth 58 mm

**Sustainability**

RoHS conform Yes

**Illustrations | Drawings**

