



EPN050

Auxiliary contact for centralised control

Technical Features

<b>Electric current</b>	
Rated current	1 A
<b>Capacity</b>	
Number of modules	0.50
<b>Use conditions</b>	
Operating temperature	-5 - 40 °C
Storage/transport temperature	-40 - 80 °C
<b>Connectivity</b>	
Type of connection	Screw terminal
<b>Connection</b>	
Cross-section flexible conductor	1 - 6 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
<b>Power</b>	
Total power loss under IN	0.10 W
<b>Dimensions</b>	
Height	85 mm
Width	8.90 mm
Depth	58 mm
<b>Sustainability</b>	
RoHS conform	Yes

Illustrations | Drawings

