



EPN050

Auxiliary contact for centralised control

Technical Features

Electric current

Rated current 1 A

Capacity

Number of modules 0.50

Use conditions

Operating temperature -5 - 40 °C

Storage/transport temperature -40 - 80 °C

Connectivity

Type of connection Screw terminal

Connection

Cross-section flexible conductor 1 - 6 mm²

Cross-section rigid conductor 1.5 - 10 mm²

Power

Total power loss under IN 0.10 W

Dimensions

Height 85 mm

Width 8.90 mm

Depth 58 mm

Sustainability

RoHS conform Yes

Illustrations | Drawings

