

**115/230V shaver socket;kb**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Output current	0 mA
----------------	------

Rated current	0.08 A
---------------	--------

**Voltage**

Output voltage	0-0 V
----------------	-------

**Use conditions**

Operating temperature	-20 - 45 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Output power	0 W
--------------	-----

Power consumption standby	0 W
---------------------------	-----

**Materials**

Colour	Knight black
--------	--------------

Surface finish	Matt
----------------	------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Coated
-----------	--------

Contains recycled material (% of total plastic weight)	0 %
--	-----

**Dimensions**

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Depth	45 mm
-------	-------

**Cable**

Cable length	0 m
--------------	-----

**Dimensions**

Built-in depth flush-mounted boxes	47 mm
------------------------------------	-------

Built-in depth	45 mm
----------------	-------

**Connection**

Connector/plug type	NEMA
---------------------	------

Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm <sup>2</sup>
--	--------------------------

Number of conduit inlets	0
--------------------------	---

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

Mounting-/Connection Position	Back
-------------------------------	------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

With claw mounting	No
--------------------	----

Mounting type	Screw mounting
---------------	----------------

Connector/plug type USB	British Standard
-------------------------	------------------

**Equipment**

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

---

**Equipment**

With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
Pre-equipped with	None

**Capacity**

Number of modules	0
-------------------	---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Suitable for**

shark	
-------	--

**Sustainability**

RoHS conform	Yes
--------------	-----