

115/230V shaver socket;kb

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Output current	0 mA
----------------	------

Rated current	0,08 A
---------------	--------

Voltage

Output voltage	0-0 V
----------------	-------

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Output power	0 W
--------------	-----

Power consumption standby	0 W
---------------------------	-----

Materials

Colour	Knight black
--------	--------------

Surface finish	Matt
----------------	------

Material	Polycarbonate (PC)
----------	--------------------

Treatment	Coated
-----------	--------

Contains recycled material (% of total plastic weight)	0 %
--	-----

Dimensions

Height	86 mm
--------	-------

Width	86 mm
-------	-------

Depth	45 mm
-------	-------

Cable

Cable length	0 m
--------------	-----

Dimensions

Built-in depth flush-mounted boxes	47 mm
------------------------------------	-------

Built-in depth	45 mm
----------------	-------

Connection

Connector/plug type	NEMA
---------------------	------

Cross-section flexible conductor without wire end sleeve	0,08 - 4 mm ²
--	--------------------------

Number of conduit inlets	0
--------------------------	---

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Mounting-/Connection Position	Back
-------------------------------	------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

With claw mounting	No
--------------------	----

Mounting type	Screw mounting
---------------	----------------

Connector/plug type USB	British Standard
-------------------------	------------------

Equipment

Connector/plug type socket outlet	British Standard
-----------------------------------	------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

With round protective earth pin	No
---------------------------------	----

Equipment	
With signal lamp	No
With lock	No
Accessories	
Has labelling field	No
Pre-equipped with	None
Capacity	
Number of modules	0
Safety	
With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20
Functions	
With orientation lighting	No
With function lighting	No
Identification	
With imprint	No
Suitable for	
shark	
Sustainability	
RoHS conform	Yes