



WXPSS81EV

IP66 Single 13A Double Pole Switched Socket for Electric Vehicle Charging

Technical Features

Electric current

Rated current	13 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Materials

Colour	Blue
RAL code	5009
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Height	86 mm
Width	86 mm
Depth	88.25 mm

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Cover, door

Type of lid	Hinged cover falls back, manual clip-in
-------------	---

Capacity

Number of modules	0
-------------------	---

Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes