



WXPSS81EV

## IP66 Single 13A Double Pole Switched Socket for Electric Vehicle Charging

### Technical Features

#### Electric current

Rated current	13 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Materials

Colour	Blue
RAL code	5009
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Untreated

#### Dimensions

Height	86 mm
Width	86 mm
Depth	88.25 mm

#### Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	Yes
With round protective earth pin	No
With signal lamp	No

#### Accessories

Has labelling field	No
---------------------	----

#### Cover, door

Type of lid	Hinged cover falls back, manual clip-in
-------------	---

#### Capacity

Number of modules	0
-------------------	---

#### Safety

Ingress Protection (IP) class	IP66
-------------------------------	------

#### Functions

With orientation lighting	No
With function lighting	No

#### Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With earth connection
Protection	Enhanced contact protection

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes