




WNA603



cubyko Light signalization white composable IP55

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 0 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Grey

RAL code 7011

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Dimensions

Height 71 mm

Width 71 mm

Depth 48 mm

Connectivity

Mounting type Screw mounting

Safety

Ingress Protection (IP) class IP55

Use conditions

Operating temperature -15 - 30 °C

Suitable for

cubyko

Sustainability

RoHS conform Yes